



高鐵路器 精密卓越



GOTECH "the best partner" to raise your competition

GT-7071-ISO 鞋材水份吸收及脫離試驗機 Insole / Insock Absorption And Desorption

EN ISO-20344、GB/T 20991、QB/T 2225、EN 12746:2000、GB/T 3903.33、ISO 22649:2003

本機用於測試鞋內底及內襯的吸水性與水解吸附性。模仿行走期間，鞋子內底所經受的撓曲過程進行試驗。採用杠桿加壓施力方式，結構設計合理，零配件加工方便；為研發改良材料提供依據。可調節水流量並通過流量計顯示水流速度；可設定測試時間，時間到達後機台自動停機。

This machine is designed for determining the water absorption and desorption of insoles and lining. The insole is flexed by simulating walking. Adopting the way to apply force by means of a lever, it is designed reasonably, so it is convenient for processing parts. It provides references for R&D to do material modification. Water flow is adjustable and its speed is displayed on the flow meter; You can set the test time, and it will stop automatically when the test time has been reached.



滾輪 Roller	直徑 in diameter(120±1)mm; 寬度 in width(50±1)mm
試樣尺寸 Specimens	(110±1) mm × (40±1) mm
速度 Speed	20±1cpm
輓子軸移動距離 Stroke	50 mm 或 or 100 mm (選擇)
水流速度 Water Flow Rate	(7.5±2.5)ml/min (出水口 water outlet)
計時器 Timer	0~999h59m59s
體積(約) Dimension	55x65x70 cm (W*D*H)
重量(約) Weight(approx.)	100kg
電源 Power	1φAC 220V 50Hz

瞭解更多產品信息，請登錄我司網站 www.gotech.biz



創於1977年
高鐵路科技股份有限公司
GOTECH TESTING MACHINES INC.

本廠: 台中市工業區24路28號
二廠: 台中市工業區24路31號
TEL: (04)23590061 FAX: (04)23591553
網址: www.gotech.biz E-mail: gt112@gotech.biz

高鐵路檢測儀器(東莞)有限公司
GOTECH TESTING MACHINES CO., LTD.

地址: 廣東省東莞市南城區宏圖高新科技開發區宏三路
TEL: 0769-89986666 22400899 FAX: 0769-22400699
E-mail: gt-d130@gotech.biz 手機: 13926831580

高特威爾檢測儀器(青島)有限公司
GOODTECHWILL TESTING MACHINES CO., LTD.

地址: 中國青島市市北區哈爾濱路52號青建太陽島1號商務樓8層
TEL: 0532-85931956 85931957 FAX: 0532-85931950
E-mail: gt-q101@gotech.biz 手機: 13708970121