





SVV 063 PA, HV gate valve, electro-pneumatic, with PI, with PV, 24 V, 50 Hz






SVV 063 PA



SVV 063 PA, HV gate valve, electro-pneumatic, with PI, with PV, 24 V, 50 Hz $\,$

- High conductance due to free clearance
- With visual indication of open and closed positions
- Service life: up to 200000 operating cycles

Dimensions



SVV 063 PA

Technical Data	SVV 063 PA, HV gate valve, electro-pneumatic, with PI, with PV, 24 V, 50 Hz
Seal: Housing	FKM
Seal: Valve seat	FKM
Feedthrough	Slideway
Opens against differential pressure of	30 hPa
Туре	HV gate valve
Valve plate	Stainless steel
Position feedback: Load capacity at 250 V AC	2 A
Housing	Aluminum
Actuator	Electro-pneumatic
Position feedback: Load capacity at 50 V DC	1.2 A
Input voltage(s)	24 V AC, 50 Hz
Tightness	1 · 10 ⁻¹⁰ Pa m ³ 1.33 · 10 ⁻⁸ 1 · 10 ⁻⁸ /s Torr l/s mbar l/s
Bakeout temperature: actuator	50 °C 122 K -223.15 °F
Conductance value with molecular flow	550 l/s
Pressure max. (absolute)	1,600 hPa 1,200 Torr 1,600 mbar
Bakeout temperature: housing	120 °C 248 K -153.2 °F
Pressure min.	1 · 10 ⁻⁷ hPa 7.5 · 10 ⁻⁸ Torr 1 · 10 ⁻⁷ mbar
Differential pressure in closing direction	1,600 hPa 1,200 Torr 1,600 mbar
Differential pressure in opening direction	1,600 hPa 1,200 Torr 1,600 mbar
Weight	3 kg 6.61 lb
Compressed air volume	160 cm ³
Pressure max. (absolute)	1,600 hPa
Power consumption	24 V DC / 5.4 W
Connection flange	DN 63 ISO-F
Closing/opening time	1.5 s/1.5 s
Compressed air (overpressure)	4 000 – 7 000 hPa
Differential pressure in closing direction	1,600 hPa
Differential pressure in opening direction	1,600 hPa
Weight	3 kg

Order number	SVV 063 PA, HV gate valve, electro-pneumatic, with PI, with PV, 24 V, 50 Hz
SVV 063 PA, HV gate valve, electropneumatic, with PI, with PV, 24 V, 50 Hz	PF E18 101



Your Success. Our Passion.

We give our best for you every day worldwide!



Are you looking for an optimum vacuum solution? Talk to us: Pfeiffer Vacuum Components & Solutions GmbH Germany T+49 551 99963-0 info-cs@pfeiffer-vacuum.com Or scan the barcode, to visit our web page:



https://webportal.pfeiffer-vacuum.com/global/en/contact



Follow Us On Social Media #pfeiffervacuum













